

Arkusz6

Gatunek	Wymiar	Waga (kg) - rzeczywista
WNLV	≠ 430 x 320	490
17NiCrMo6-4	□ 200	520
20MnMoNi4-5	≠ 200 x 140	250
45	□ 200	360
20H2N4A	□ 300	220
25CrMo4	□ 260	360
NC7V3	□ 300	300
20MnMoNi4-5	□ 400	1250
30G2HMB	≠ 300 x 145 (7 szt)	3460
WNLV	□ 300	660
10	□ 380	970
100CrMnMoSi8-4-	∅ 250	1166
4130	∅ 300	325
17NiCrMo6-4	∅ 340	360
34CrNiMo6	∅ 300	220
34HNM	∅ 300	270
17NiCrMo6-4	∅ 450	2260
8822H	∅ 400	360
45	∅ 340	340
30G2HMB	≠ 370 x 200	1000
50HF	≠ 320 x 270	430
WNLV	≠ 260 x 210	540
30G2HMB	≠ 260 x 140	420
30G2HMB	□ 160	300
30G2HMB	□ 160	480
50HS	∅ 180	590
30CrNiMo8	□ 450	420
WNL	≠ 240 x 150	290
A182F5a	□ 300	580
R260V	≠ 220 x 155	190
30CrNiMo8	∅ 250	190
WNL	≠ 300 x 130	160
R220	≠ 320 x 210	320
30CrNiMo8	∅ 280	215
45HN	□ 300	215
15NiCuMoNb5-6-4	□ 220	440
20H2N4A	∅ 180	330
4330	∅ 280	1250
40HNM	∅ 210	470
35	∅ 200	260
40H	∅ 180	210
20H2N4A	∅ 180	260

Arkusz6

40HNMA	∅ 170	230
WCL	∅ 180	370
WNLV	∅ 235	460
30Mn5	□ 160	570
4130	≠ 210 x 190	560
NC7VL	□ 200	370
30G2HMB	□ 200	370
WCL	□ 200	315
22H2NM	≠ 190 x 150	350
30H	□ 200	670
30G2HMB	≠ 275 x 160	445
30G2HMB	≠ 220 x 145	360
20H2N4A	□ 250	260
20H2N4A	∅ 190	250
45	∅ 220	310
45	∅ 300	380
22	∅ 180	200
8822H	∅ 240	350
8630	∅ 295	340
NC7VL	∅ 175	190
8822H	∅ 240	345
8822H	∅ 230	232
38HMJ	∅ 190	130
NC7V3	∅ 170	145
St35	∅ 210	245
50HS	∅ 180	180
35	□ 200	300
45	∅ 200	150
30CrNiMo8	∅ 255	230
4145H	∅ 260	200
45	∅ 230	175
25CrMo4	∅ 250	260
40HNMA	∅ 265	260
25CrMo4	□ 260	300
30CrNiMo8	∅ 200	145
8822H	∅ 200	200
4145H	∅ 255	200
34CrNiMo6	∅ 310	240
15HN	∅ 230	260
50HS	∅ 215	250
8822H	∅ 240	200
35SG	∅ 250	210
4130	∅ 190	150

Arkusz6

60	∅ 235	135
4145H	∅ 260	210
34CrNiMo6	∅ 220	170
45H	≠ 210 x 110	180
15HN	≠ 240 x 190	165
45	∅ 220	170
45	□ 165	150
30H	≠ 190 x 170	120
15HN	∅ 300	170
35	□ 200	190
WNL	≠ 270 x 220	280
WCLV	≠ 260 x 190 (2szt.)	190
34CrNiMo6	≠ 220 x 110	180
WCL	□ 255	470
15NiCuMoNb5-6-4	∅ 395	320
WCL	∅ 395	240
WCL	∅ 320	160
20H2N4A	□ 300	125
NC7V3	□ 300	330
40HNMA	∅ 310	250
55NiCrMoV7	∅ 230	150
55NiCrMoV7	∅ 230	170
WNLV	□ 210	360
40H	∅ 135	120
40HNMA	∅ 120	100
50HS	□ 180	340
30CrNiMo8	∅ 200	195
18G2ANi	□ 200	430
40H	∅ 200	150
40H	∅ 190	370
18G2ANi	□ 220	500
20H2N4A	□ 130	230
15HN	∅ 205	240
86B30H	∅ 225	390
15NiCuMoNb5-6-4	∅ 200	300
25CrMo4	∅ 200	300
8822H	∅ 180	330
NC7VL	∅ 200	400
40H	∅ 190	230
35SG ?	∅ 210	400
45	∅ 100	120
11CrMo9-10	∅ 50 x 5720 (16 szt.)	1405
20H2N4A	□ 80 x 2860 (3 szt.)	430

Arkusz6

13CrMo4-5	∅ 42 x 6180 (100 szt.)	6735
18G2A	∅ 115 x 6000 (16 szt.)	7820
18G2A	∅ 40 x 6000 (7 szt.)	415
20HG	□ 140 x 3000 (7szt.)	3230
40HNMA	□ 110	130
45	□ 160	120
40HNMA	∅ 140	180
25HM	□ 110	120
45HNMF	□ 110	120
45	∅ 135	115
P290GH	∅ 180	125
35SG	□ 200	310
DHQ1	∅ 400 x 840	825
50CrMo4	∅ 270 x 1715	770
DHQ1	∅ 460 x 1100	1430
100CrMnSi6-4	∅ 200 x 2350	575
WCL	∅300 x ∅130 x 315 (2szt.)	360
R220	≠ 250 x 190 x 1460	540